



Drawings:
 General Schematic: #28789
 Customer Connection: #25027-3
 Interface/Display Module: #28283-1
 Current Transformer: 26461

- Notes:
- 1.) The "A" mounting holes are mandatory, the "B" holes are optional.
 - 2.) Weight lbs (Kg): 671 (304)
 - 3.) Maintain 3 Inch Side Clearance
 - 4.) For wire entry a foam gland is provided 9 inches from the back, running across the bottom.
 - 5.) The 50A unit is rated for 39A when applied with a 480V/600V autotransformer.
 - 6.) The 100A unit is rated for 78A when applied with a 480V/600V autotransformer.

Size	Watt Loss	Btu/h
50 Amp	2,676	9,131
100 Amp	3,500	11,942

WARNING: Filter must be securely anchored to the floor to avoid a tipping hazard!

				TOLERANCES (EXCEPT AS NOTED)	TCI W132 N10611 Grant Drive Germantown, WI 53022
				DECIMAL	
				.XX ± .05	Outline/Installation, Active Filter 50-100 Amp, Type 12, Floor Mgt
				.XXX ± .025	
				FRACTIONAL	DRN. BY: RHW DATE: 7/24/17 105368
				± 1/16	
				ANGULAR	SCALE: .04 APRVD: SIZE A
NO	REVISION	DATE	BY	± 1°	SHT. 1 OF 1

2

1

2

1